Eaton BRP20L125G

Catalog Number: BRP20L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X2, Aluminum, NEMA 1,10kAlC, BR2125,40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al

General specifications

Product Name

Eaton BR main lug loadcenter

UPC

786689053239

Product Height

3.88 in

Product Weight

19.4 lb

Certifications

UL 50 UL 67

Catalog Number

BRP20L125G

Product Length/Depth

21 in

Product Width

14.31 in

Warranty

10 year



Product specifications

Number of spaces

20

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

BR2125

Enclosure

NEMA 1

Amperage Rating

125 A

Number Of Poles

Single-pole

Enclosure material

Metallic

Type

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires
Two hots, neutral and ground

Number of circuits 40

..

Voltage rating

120/240V

Box size

X2

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20L125G



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia