

# Eaton BRP30B200R

Catalog Number: BRP30B200R

Eaton BR main breaker loadcenter, Plug-on, 200A,X6,Aluminum, Cover included,NEMA 3R, Metallic, 10 kAIC, BR, 60 circuits, Single pole,30 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers,120/240V



## General specifications

|                                  |                      |
|----------------------------------|----------------------|
| Product Name                     | Catalog Number       |
| Eaton BR main breaker loadcenter | BRP30B200R           |
| UPC                              | Product Length/Depth |
| 786689059347                     | 34.12 in             |
| Product Height                   | Product Width        |
| 5.5 in                           | 14.31 in             |
| Product Weight                   | Warranty             |
| 22 lb                            | 10 year              |

## Certifications

UL 67  
UL 50

## Product specifications

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

60

### Number Of Poles

Single-pole

### Number of spaces

30

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X6

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30B200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)