

Eaton BRP30BC200

Catalog Number: BRP30BC200

Plug-on neutral main circuit breaker loadcenter, 200A, X6, Copper, Cover included, NEMA 1, Metallic, 25 kAIC, CSR2200, 60 circuits, Single pole, 30 spaces, Two hots, a neutral, and a ground, Single-phase, Combination, Type BR 1-inch breakers, 120/240V

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30BC200
UPC	Product Length/Depth
786689052850	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
32.6 lb	10 year
Certifications	
UL 50 UL 67	

Product specifications

Number of spaces

30

Interrupt rating

25 kAIC

Phase

Single-phase

Bus material

Copper

Main circuit breaker

CSR2200

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type

Plug-on neutral main circuit breaker loadcenter

Cover

Cover included

Used with

Type BR 1-inch breakers

Number of wires

Two hots, neutral and ground

Number of circuits

60

Voltage rating

120/240 V

Box size

X6

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30BC200](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)