Eaton BRP30L200G

Catalog Number: BRP30L200G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 200 A, X5, Aluminum, Gray, NEMA 1, Metallic, 10kAlC, CSR, Surface, flush, NEMA 1, 60 Circuits, Single-pole, 30 Spaces, Two hots, a neutral, and a ground, Single-phase

General specifications

Product Name

Eaton BR main lug loadcenter

UPC

786689044084

Product Height

3.88 in

Product Weight

26.2 lb

Certifications

UL 50 UL 67

Catalog Number

BRP30L200G

Product Length/Depth

29.12 in

Product Width

14.31 in

Warranty

10 year



Product specifications

Number of spaces

30

Special features

Ground bar

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Color

Gray

Main circuit breaker

CSR

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Surface, flush

Enclosure material

Metallic

Type

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP30L200G

Number of circuits

60

Voltage rating

120/240V

Box size

X5



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia