

Eaton BRP30N200R

Catalog Number: BRP30N200R

Eaton BR convertible loadcenter, Converible, 200 A, X6, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 60 Circuits, Single-pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30N200R
UPC	Product Length/Depth
786689059378	35.7 in
Product Height	Product Width
5.7 in	15.5 in
Product Weight	Warranty
33.25 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel	Resources
Type	Brochures
Converible	Loadcenters and Circuit Breakers
Amperage Rating	Specifications and datasheets
200 A	Eaton Specification Sheet - BRP30N200R
Bus material	
Aluminum	
Cover	
Cover included	
Main circuit breaker	
BR	
Mounting	
Combination	
Number of circuits	
60	
Number Of Poles	
Single-pole	
Number of spaces	
30	
Phase	
Single-phase	
Used with	
Type BR 1-inch breakers	
Voltage rating	
120/240 V	
Box size	
X6	
Enclosure	
NEMA 3R	
Enclosure material	
Metallic	
Interrupt rating	
10 kAIC	
Number of wires	
3	



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)