

Eaton BRP30N200RG

Catalog Number: BRP30N200RG

Eaton BR convertible loadcenter,Ground bar,Converible,200 A,X6,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,Combination,60 Circuits,Single-pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30N200RG
UPC	Product Length/Depth
786689059385	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
22 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Ground bar

Type

Converible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30N200RG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP30N200RG

Catalog Number: BRP30N200RG

Eaton BR convertible loadcenter,Ground bar,Converible,200 A,X6,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,Combination,60 Circuits,Single-pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30N200RG
UPC	Product Length/Depth
786689059385	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
22 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Ground bar

Type

Converible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30N200RG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia