# Eaton BRP40B200

## Catalog Number: BRP40B200

Eaton BR main breaker loadcenter, Ground bar, includes BREQS125 holddown screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 80 circuits, Single pole, 40 spaces

## General specifications

Product Name	Catalog I
Eaton BR main breaker loadcenter	BRP40B
UPC	Product I
786689044053	39 in
Product Height	Product V
3.88 in	15.5 in
Product Weight	Warranty
27 lb	10 year
Certifications UL 67 UL 50	

Catalog Number BRP40B200 Product Length/Depth 39 in Product Width 15.5 in Warranty



## Product specifications

### Number of spaces

40

Special features

Ground bar, includes BREQS125 hold-down screw

Interrupt rating

25 kAIC

Phase

Single-phase

**Bus material** 

Aluminum

Main circuit breaker

CSR

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type Plug-on neutral main circuit breaker loadcenter

#### Cover

Cover included

Used with Type BR 1-inch breakers

**NEMA** rating

NEMA 1

Number of circuits

80

Voltage rating 120/240 V

## Resources

Brochures Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP40B200



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia