

# Eaton BRP40BC200

Catalog Number: BRP40BC200

Plug-on neutral main circuit breaker  
loadcenter,200A,X8,Copper,Cover included,NEMA  
1,Metallic,25kAIC,CSR2200,80 circuits,Single pole,40 spaces,Two  
hots, a neutral, and a ground,Single-  
phase,Gray,Combination,NEMA 1,Type BR 1-inch breakers,12



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP40BC200
<b>UPC</b>	<b>Product Length/Depth</b>
786689052973	39 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
37.5 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Copper

### Cover

Cover included

### Main circuit breaker

CSR2200

### Number of circuits

80

### Number Of Poles

Single-pole

### Number of spaces

40

### Phase

Single-phase

### Accessories

copper bus

### Enclosure color

Gray

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X8

### Enclosure

NEMA 1

### Enclosure material

Metallic

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP40BC200

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)