Eaton BRP40E200G

Catalog Number: BRP40E200G

Eaton BR convertible loadcenter, Convertible, lugs installed | Ground bar, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Two hots, a neutral, and a ground, Single-phase, #6-1/0 AWG Cu/Al

General specifications

Product Name Eaton BR convertible loadcenter
UPC 786689055028
Product Height 3.88 in
Product Weight 32.1 lb
Certifications UL 50 UL 67

Catalog Number BRP40E200G Product Length/Depth 39 in Product Width 14.31 in Warranty 10 year



Product specifications

Number of spaces

40

Special features

Convertible, lugs installed Ground bar

Interrupt rating

25 kAIC

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/AI

Bus material

Aluminum

Main circuit breaker

CSR

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type Convertible, lugs installed

Cover Cover included

Used with Type BR 1-inch breakers

Number of wires Two hots, neutral and ground

Number of circuits

80

Resources

Brochures Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP40E200G

Voltage rating

120/240 V

Box size

X8



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2023 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2023 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia