

# Eaton BRP40L200

Catalog Number: BRP40L200

Eaton Eaton Type BR plug-on neutral loadcenter, 200 A, MLO, 40 spaces, 120/240 V, Two hots, a neutral, and a ground wire, 10kAIC, NEMA 1, Single Pole

## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP40L200
UPC	Product Length/Depth
786689052980	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
30.3 lb	10 year
Certifications	
UL 50 UL 67	



## Product specifications

### Number of spaces

40

### Interrupt rating

10 kAIC

### Phase

Single-phase

### Bus material

Aluminum

### Color

Gray

### Main circuit breaker

CSR2200

### Enclosure

NEMA 1

### Amperage Rating

200 A

### Number Of Poles

Single-pole

### Mounting

Surface, flush

### Enclosure material

Metallic

### Type

MLO

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### NEMA rating

NEMA 1

### Number of wires

Two hots, neutral and ground

### Number of circuits

80

### Voltage rating

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP40L200](#)

120/240V

Box size

X6



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)