# Eaton BRP40L200G

## Catalog Number: BRP40L200G

Eaton BR main lug loadcenter, Ground bar, Main lug only, 200 A, X6, Aluminum, Gray, NEMA 1, Metallic, 10kAIC, CSR2200, Surface, flush, 80 Circuits, Twenty-four pole, 40 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V, #1–300 kcmil

#### General specifications

**Product Name** 

Eaton BR main lug loadcenter

**UPC** 

786689052997

Product Height

3.88 in

**Product Weight** 

30.3 lb

Certifications

UL 50 UL 67

Catalog Number

BRP40L200G

Product Length/Depth

34.12 in

**Product Width** 

14.31 in

Warranty

10 year



### Product specifications

Number of spaces

40

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Color

Gray

Main circuit breaker

CSR2200

**Enclosure** 

NEMA 1

Amperage Rating

200 A

**Number Of Poles** 

Single-pole

Mounting

Surface, flush

Enclosure material

Metallic

Туре

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

**NEMA** rating

NEMA 1

Number of wires

Two hots, neutral and ground

Number of circuits

80

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP40L200G

Voltage rating

120/240V

Box size

X6



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia