# Eaton BRP40L200R

## Catalog Number: BRP40L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X6, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

#### General specifications

**Product Name** 

Eaton BR main lug loadcenter

**UPC** 

786689059040

Product Height

34.13 in

**Product Weight** 

22 lb

Certifications

UL 67 UL 50

Catalog Number

BRP40L200R

Product Length/Depth

3.88 in

Product Width

14.31 in

Warranty

10 year



### Product specifications

Number of spaces

40

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

BR

**Enclosure** 

NEMA 3R

Amperage Rating

200 A

**Number Of Poles** 

Single-pole

**Enclosure material** 

Metallic

Type

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

**NEMA** rating

NEMA 3R

Number of wires

3

Number of circuits

80

Voltage rating

120/240V

Box size

Х6

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP40L200R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia