

# Eaton BRP40N200RG

Catalog Number: BRP40N200RG

Eaton BR convertible loadcenter,Ground bar,Converible,200 A,X8,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,Combination,80 Circuits,Single-pole,40 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200RG
UPC	Product Length/Depth
786689059064	3.88 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel	Resources
<div>Special features</div> <div>Ground bar</div>	<div>Brochures</div> <div>Loadcenters and Circuit Breakers</div>
<div>Type</div> <div>Converible</div>	<div>Specifications and datasheets</div> <div>Eaton Specification Sheet - BRP40N200RG</div>
<div>Amperage Rating</div> <div>200 A</div>	
<div>Bus material</div> <div>Aluminum</div>	
<div>Cover</div> <div>Cover included</div>	
<div>Main circuit breaker</div> <div>BR</div>	
<div>Mounting</div> <div>Combination</div>	
<div>Number of circuits</div> <div>80</div>	
<div>Number Of Poles</div> <div>Single-pole</div>	
<div>Number of spaces</div> <div>40</div>	
<div>Phase</div> <div>Single-phase</div>	
<div>Used with</div> <div>Type BR 1-inch breakers</div>	
<div>Voltage rating</div> <div>120/240 V</div>	
<div>Box size</div> <div>X8</div>	
<div>Enclosure</div> <div>NEMA 3R</div>	
<div>Enclosure material</div> <div>Metallic</div>	
<div>Interrupt rating</div> <div>10 kAIC</div>	



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)