

Eaton BRP42NC225R

Catalog Number: BRP42NC225R

Eaton BR convertible loadcenter, Convertible, 225 A, X10, Copper, Cover included, NEMA 3R, Metallic, 25 kAIC, BR, Combination, 84 Circuits, Single-pole, 42 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP42NC225R
UPC	Product Length/Depth
786689365622	5.25 in
Product Height	Product Width
48 in	14.31 in
Product Weight	Certifications
31.5 lb	UL 67
	UL 50

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Copper

Cover

Cover included

Mounting

Surface

Number Of Poles

Single-pole

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X10R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP42NC225R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)