


Specifications



Photo is representative



Eaton BRP60B200R

Plug-on neutral main circuit breaker loadcenter, 200A, X10, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 120 circuits, Single pole, 60 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP60B200R
UPC	786689059088
PRODUCT LENGTH/DEPTH	48.75 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	35 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

TYPE	Plug-on neutral main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	120
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	60
PHASE	Single-phase
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X10
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3
NEMA RATING	NEMA 3R

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP60B200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

