

Eaton BRSN220

Catalog Number: BRSN220

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch switching neutral breaker, 20 A, 10 kAIC, Two-pole, 120V, BR, Switching neutral, #14-4 AWG Cu/Al, BR, Type BR Loadcenters



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRSN220
	UPC
	786676364553
Product Length/Depth	Product Height
2 in	2.5 in
Product Width	Product Weight
3 in	0.6 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch switching neutral breaker

Special features

Used with Type BR Loadcenters

Amperage Rating

20 A

Voltage rating

120 V

Trip Type

Switching Neutral

Circuit breaker type

BR

Used with

Type BR Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRSN220](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)