

Eaton BRSUR3040N200

Catalog Number: BRSUR3040N200

Eaton BR surge loadcenter, Factory integrated surge, Convertible main, 200 A, L1, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 30/40 Circuits, 30 Spaces, Three-wire, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR surge loadcenter	BRSUR3040N200
UPC	Product Length/Depth
782116417124	3.88 in
Product Height	Product Width
39 in	14.31 in
Product Weight	Warranty
39 lb	10 year

Certifications

UL 67
UL 50

defaultTaxonomyAttributeLabel

Special features

Factory integrated surge

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Voltage rating

120/240 V

Box size

L1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRSUR3040N200](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)