

# Eaton BRSUR4040B200

Catalog Number: BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V



## General specifications

Product Name	Catalog Number
Eaton BR surge loadcenter	BRSUR4040B200
UPC	Product Length/Depth
782116417148	3.88 in
Product Height	Product Width
45 in	14.31 in
Product Weight	Warranty
45 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

Factory integrated surge

### Type

Main circuit breaker

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Mounting

Combination

### Number of circuits

40

### Number of spaces

40

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

L2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRSUR4040B200](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)