

Eaton BRX2110

Catalog Number: BRX2110

Eaton BR thermal magnetic circuit breaker, thermal-magnetic circuit breaker, 110 A, 65 kAIC, Two-pole, 120/240V, BRX, #14-2/0 AWG, BRX, 65 kAIC, 50-60 Hz



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRX2110
	UPC
	786685926810
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
2 in	0.5 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL Listed file E7819

Type

thermal-magnetic circuit breaker

Amperage Rating

110 A

Voltage rating

120/240 V

Circuit breaker type

BR

Frequency rating

50-60 Hz

Capacity

65 kAIC

Interrupt rating

65 kAIC

Main circuit breaker

BR

Wire size

#14-2/0 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Type BRX thermal-magnetic circuit breaker](#)

[Eaton Specification Sheet - BRX2110](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)