Eaton BSPMA3480WYGR

Catalog Number: BSPMA3480WYGR

Eaton Bussmann series BSPM series surge arrestor, Technology type MOV, 277/480 V, Surge arrestor, Thermoplastic, UL94V2, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

General specifications



Product Name

Eaton Bussmann series BSPM series

surge arrestor

UPC

051712709095

Product Length/Depth

2.13 in

Product Width

2.56 in

Warranty

Five year limited waranty

Catalog Number BSPMA3480WYGR

0. 0

Product Height

3.54 in

Product Weight

0.73 lb

Compliances

Contact factory RoHS Compliant

Certifications

UL 94V0

UL Listed



Product specifications

Special features

Technology type MOV

Material

Thermoplastic

Enclosure

Thermoplastic, UL94V2

Surge current

200 kA

Mounting Method

35 mm DIN rail

Nominal Discharge Current

20 kA

Short-circuit rating

200 kA

Type

Surge arrestor

Operating voltage

550

Indicator type

Remote contact

Frequency rating

50/60 Hz

Operating temperature

-35 to 85 °C

Voltage rating

277/480 V

Application

Surge Protection

Degree of protection

IP20

Resources

Catalogs

BSPMA3480WYGR~277/480 Wye, 3P

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - BSPMA3480WYGR



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia