



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



BSV10XQ 12-10 Vinyl Ins Butt Splice Ylw *Panduit Corporation*

Catalog Number	BSV10XQ
Manufacturer	Panduit Corporation
Description	Panduit BSV10X-Q Vinyl Insulated Butt Splice
Weight per unit	0.0090 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Expanded
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	12 - 10
------	---------

Descriptions

Description	12-10 VINYL INS BUTT SPLICE YLW
extra long description	PAN BSV10X-Q Pan-Term® BSV10X-Q But
Long Description	Panduit BSV10X-Q Vinyl Insulated Butt Splice
Product Type	Pan-Term® BSV10X-Q Butt Splice, Yellow, Vinyl, 10-12 Awg, PK

Manufacturer Information

Brand	PANDUIT
GTIN	00074983521616
Manufacturers Part Number	BSV10X-Q
UPC	074983521616

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Butt Splice

Availability

minimum qty	25
-------------	----

Packaging

Carton	25
Package	250
Weight Per each	0.009



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Uses, Certifications, and Standards

Mounting	5/16
standard	UL 486C, CSA C22.2 No.65
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)