



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT1MC0 Nylon Cable Tie *Panduit Corporation*

Catalog Number	BT1MC0
Manufacturer	Panduit Corporation
Description	
Weight per unit	1.0 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	78598846579
Material	Weather-Resistant Nylon 6-6
Tensile Strength	51330

Material, Color, and Finish

Color	BLACK
-------	-------

Dimensions and Weight

Length	4 in
Thickness	0.04 in
Width	DIMMING LINEAR FLUORESCENT BALLAST, 9.5 INCH L X 1.71 INCH W X 1.2 INCH D SIZE; 50 DEG F MIN. STARTING TEMPERATURE; 10 PERCENT MAX. THD; 50/60 HZ FREQUENCY RATING; UL, CSA APPROVAL; 1 LAMP(S); T8 LAMP TYPE; 32 W LAMP WATTAGE; 120/277 VAC INPUT VOLTAGE

Descriptions

Description	NYLON CABLE TIE
Product Type	Ctie, Mbarb, 4L, Mini, WR, BL, PK100
Special Features	Outdoor (UV Resistant)

Manufacturer Information

Brand	PANDUIT CORPORATION
GTIN	00074983413034
Manufacturers Part Number	BT1M-C0
sub brand	Dome-Top
UPC	074983413034

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Ties



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685


Packaging

Carton	100
Package	1000
Weight Per each	1

Uses, Certifications, and Standards

Application	General
standard	UL Compliant 62275, UL Listed #E56854

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. (mm)	MAX. (mm)									
BT1M	.06 (1.5)	0.90 (23)	.036 (0.9)	.095 (2.4)	.110 (2.8)	.156 (4.0)	.172 (4.4)	4.0 (102)	18 (80)	MINIATURE	.05 (22)
BT1.5M	.06 (1.5)	1.5 (38)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	6.3 (160)	18 (80)	MINIATURE	.09 (43)
BT2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	18 (80)	MINIATURE	.12 (53)
BT4M	.06 (1.5)	4.00 (102)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	14.2 (361)	18 (80)	MINIATURE	.21 (93)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .10 (2.5) (.XXX) ± .020 (.51)
(.XX) ± .02 (.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
PMH

MAT'L:

SCALE
NONE

DATE
6-24-93

NYLON 6.6

DRAWING NO.
BT-0037
SHEET 1 OF 3

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
10	5/2/06	JABO		REMOVED STRAIGHT TIP REFERENCE & TIP STYLE COLUMN	0037	10		