The Bullet® flood you love, now in LED.

Perfect for residential and commercial landscapes.



BULLET12






BULLET12

- Available in single or dual head configurations
- Each equivalent to 75W BR/Halogen/Wide Flood
- Professional grade with adjustable heads
- Mount as a downlight or uplight on RAB Mighty Post or junction box
- · Available in bronze, white, black and verde green
- Microprismatic diffusion lens for smooth and even light distribution that eliminates glare
- Integrated TRIAC and ELV dimming
- DLC™ qualified (cool and neutral models)
- 5-Year warranty
- 100,000-Hour LED Lifespan

Photometrics

BULLET12 - At 5 foot setback, 45° above horizontal



Multiples of Mounting Height • Values Shown in Footcandles
Photometric Report #ITL80692



Specifications

UL Listing: Suitable for wet locations

Suitable for mounting within 1.2m (4 ft.) off the ground

LEDs: Multi-chip, high-output, long-life LEDs

Driver: Innovative integrated driver technology with 120V TRIAC and ELV dimmina*

Lifespan: 100,000-Hour LED Lifespan based on IES LM-80 results and TM-21 calculation

SINGLE BULLET12:

Nominal Watts @120V	12W
Input Watts	13
Output Lumens**	957
Lumens Per Watt**	74
Color Accuracy (CRI)**	84
Color Temperature (CCT)**	4000K

Thermal Management: Superior heat sinking with external Air-Flow fins

Housing: Die-cast aluminum housing, lens frame & mounting plate

Reflector: Semi-specular, vacuum-metalized polycarbonate

Lens: Microprismatic diffusion lens for smooth and even light distribution

Mounting: Heavy-duty mounting arm with "O" ring seal & stainless steel screws

Gaskets: High-temperature silicone gaskets

Finish: Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contain no VOC or toxic heavy metals.

Color Uniformity: RAB's range of CCT (Correlated Color Temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2011.

Color Stability: RAB LEDs exceed industry standards for chromatic stability

Green Technology: Mercury and UV free, and RoHS compliant. Polyester powder coat finish formulated without the use of VOC or toxic heavy metals.

IESNA LM-79 & LM-80 Testing: RAB LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80, and have received the Department of Energy "Lighting Facts" label.

California Title 24: BULLET12 complies with 2013 California Title 24 building and electrical codes as a residential outdoor lighting fixture with no additional hardware required and as a commercial outdoor non-pole-mounted fixture < 30 Watts when used with a photosensor control. Select catalog number PCS900(120V) or PCS900/277 to order a photosensor.

BULLET2x12 complies with 2013 California Title 24 building and electrical codes as a residential outdoor lighting fixture with no additional hardware required and as a commercial outdoor non-pole-mounted fixture < 30 Watts when used with a photosensor control. Select catalog number PCS900(120V) or PCS900/277 to order a photosensor.

Dimensions & Weight

BULLET12 Weight: 1.5 kg.



Ordering Information

Product Family	Wattage		Color Temperature		Finish	
BULLET						
	12	12W	Blank	5000K	Α	Bronze
	2X12	24W	N	4000K	W	White
			Υ	3000K	В	Black
					VG	Verde Green

^{*} Visit rabweb.com for a complete list of compatible dimmers.

^{**} Values shown for neutral temperature. Visit rabweb.com for cool and warm.