

Eaton BWH2100

Catalog Number: BWH2100

Eaton Type BR Main Circuit Breaker, Main circuit breaker, 100 A, 25 kAIC, Two-pole, 120/240 V, BR, #2 AWG-300 kcmil
Cu/Al, BR, BW, Used in ECB Unit Enclosure



General specifications

Product Name

Eaton BW main breaker

Catalog Number

BWH2100

UPC

782116061105

Product Length/Depth

6.25 in

Product Height

5.25 in

Product Width

5.25 in

Product Weight

2.75 lb

Warranty

Limited lifetime residential, 1 year commercial

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

Catalog Notes

Series combination rating with Types BD, BR, BQ, BQC and GFCB is 22,000 AIC with BRH main and 25,000 AIC with BWH main.

Type

Main circuit breaker

Amperage Rating

100 A

Voltage rating

120/240 V

Circuit breaker type

BR

Circuit breaker frame type

BW

Used with

Used in ECB Unit Enclosure

Interrupt rating

25 kAIC

Main circuit breaker

BR

Wire size

#2 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BWH2100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)