

# Eaton BWH2200

Catalog Number: BWH2200

Eaton Type BR Main Circuit Breaker, Main circuit breaker, 200 A, 25 kAIC, Two-pole, 120/240 V, BR, #2 AWG-300 kcmil  
Cu/Al, BWH, MHM200P, MHM200B, MHR200P, MHR200B, MHM200P1N4N4N



Photo is representative

## General specifications

Product Name

Eaton BW main breaker

UPC

786676460606

Product Height

5.25 in

Product Weight

2.75 lb

Compliances

Federal Specifications Classification W-C375

Catalog Number

BWH2200

Product Length/Depth

6.25 in

Product Width

5.25 in

Warranty

Limited lifetime residential, 1 year commercial

Certifications

UL 489

Catalog Notes

Series combination rating with Types BD, BR, BQ, BQC and GFCB is 22,000 AIC with BRH main and 25,000 AIC with BWH main.

Type

Main circuit breaker

Amperage Rating

200 A

Voltage rating

120/240 V

Circuit breaker frame type

BWH

Used with

MHM200P, MHM200B, MHR200P, MHR200B,  
MHM200P1N4N4N

Interrupt rating

25 kAIC

Main circuit breaker

BR

Wire size

#2 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BWH2200](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)