






4 3 2 1



TERMINAL SCREWS ARE COMBINATION 8-32 PHIL-SLOT-1/4" HEX WITH SEMS WASHER



MAIN PRODUCT IDENTIFICATION LABEL




**Chlor-Hammer** INDUSTRIAL CONTROL TRANSFORMER  
 100VA 50/60Hz  
 TEMP CL. 105°C  
 CAT. C0100E1B  
 SERIES 2  
 420833

Transformer Specifications	
PRIMARY VOLTAGE(S)	120/240
SECONDARY VOLTAGE(S)	24
RATED V.A.	100
RATED FREQUENCY	50/60
INSULATION CLASS	105
AGENCY APPROVALS	UL/CUL
ESTIMATED WEIGHT	4.4 LBS

TEST REQUIREMENTS	
WINDING	H4-H3 H2-H1 X2-X1
D.C. VOLTS	120 120 26.1
LOAD VOLTS	120 120 24
F.L. AMPS	0.537 0.537 4.167
HI-POT	3000V 1800V
EXCITING AMPS	0.71AMPS @ 120 VOLTS, 50HZ
EXCITING WATTS	7/2 MAX



REVISION	DATE	BY	DESCRIPTION
1	07/01/09	S. CASTRO	DATE

UNLESS OTHERWISE SPECIFIED	DRAYER/DESIGNER	DATE
DIMENSIONS IN INCHES	S. CASTRO	07/01/09
ONE PLACE DEC	APP'D	07/01/09
TWO PLACE DEC	E. ROBLES	07/01/09
THREE PLACE DEC	APP'D	07/01/09
ANGLES	0.5/ANODVAL	DATE
VOLTAJE	ENGR REF	07/01/09
TOLERANCE		
APPROXIMATE		
FORCE/TORQUE/SPEED		
TEMPERATURE		
DIMENSIONS TO BE INTERPRETED IN ACCORDANCE WITH		
ASME Y14.5M-1994		
UNLESS OTHERWISE SPECIFIED		
STANDARD DIMENSIONS		
PER SERIES 220		
PROVISION		

SIZE	SCALE	PARTS LIST	DWG NO	PRODUCT CODE	SHEET NO
B	1:1		C0100E1B.DWG	C0100E1B	1 OF 1

4 3 2 1

EA0 JAGAL FRM01 REV. 05/03/08 4 3 2 1 © 2008 Eaton Corporation. All Rights Reserved