



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



C0100E2B 100 Va Mte CTRL XFRMR 240X480V-24V *Eaton Corp*

Catalog Number	C0100E2B
Manufacturer	Eaton Corp
Description	Eaton Type Mte, Industrial Control Transformer, PV: 240V X 480V, SV: 24V, 55°C, 100 Va
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.4900 IN X 3.3800 IN X 3.3600 IN
kva rating	100 VA
Primary Voltage	240 V x 480 V
Secondary Voltage	24 V
Tap Size	NONE

Descriptions

Description	100 VA MTE CTRL XFRMR 240X480V-24V
extra long description	ETN C0100E2B 100 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton type MTE, industrial control transformer, pv: 240v x 480v, sv: 24v, 55°C, 100 va
Product Type	100 Va Type Mte Control Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680422768
Manufacturers Part Number	C0100E2B
UPC	786680422768

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390

Packaging

Carton	1
Weight Per each	3.5

Uses, Certifications, and Standards

Application	Other
standard	CSA Certified,cUL Certified,UL Listed,RoHS Compliant
Temperature Rating	55°C