



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C01045 8X10 Combo Module RJ45 W/RJ31X

Pass & Seymour/Legrand

Catalog Number	C01045
Manufacturer	Pass & Seymour/Legrand
Description	The 10X8 Combo Distributes Up to 4 Incoming Telephone Lines (RJ45) to 10 Locations, and 1 GHZ Video to Eight Locations. The Innovative Mounting Bracket Includes A Detachable Platform For The Coax Splitter, Allowing Easy Access to All Termination Ports Dur
Weight per unit	1.5 (lbs/each)
Product Category	20130813155925

Features

connection	RJ45, F Connector, RJ31X
Material	18 Gauge Cold Rolled Steel
Number of Ports	10 Telecom, 8 Video, 1 Security
Port Type	RJ45(10), F Connector(8), RJ31X(1)

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Height	5 inches
Width	6 inches

Descriptions

Description	8X10 COMBO MODULE RJ45 W/RJ31X
extra long description	OnQ C01045 8X10 COMBO MODULE RJ45 W
Long Description	The 10x8 combo distributes up to 4 incoming telephone lines (RJ45) to 10 locations, and 1 GHz video to eight locations. The innovative mounting bracket includes a detachable platform for the coax splitter, allowing easy access to all termination ports dur
Product Type	8X10 Combo Module RJ45 W/RJ31X
Special Features	8 way passive digital HDTV cable splitter. 6 kV ring wave surge protection on all coax ports. 1x10 4-line RJ45 telecom module. RJ31X security line interface.

Manufacturer Information

Brand	Pass & Seymour
GTIN	00804428066897
Manufacturers Part Number	C01045
sub brand	On-Q
UPC	804428066897



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Telecom/Video Module

Packaging

Carton	1
Package	10
Weight Per each	1.51

Uses, Certifications, and Standards

Application	Residential
Mounting	ENCLOSURE
Operating Temperature	-40 to 140 F