



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291



C0250E2B 250 Va Mte CTRL XFRMR 240X480V-24V *Eaton Corp*

Catalog Number	C0250E2B
Manufacturer	Eaton Corp
Description	Eaton Type Mte, Industrial Control Transformer, PV: 240V X 480V, Taps: None, SV: 24V, 55°C, 250 Va
Weight per unit	10.0 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	4.1800 IN X 4.5000 IN X 4.2200 IN
kva rating	250 VA
Primary Voltage	240 V x 480 V
Secondary Voltage	24 V
Tap Size	NONE

Descriptions

Description	250 VA MTE CTRL XFRMR 240X480V-24V
extra long description	ETN C0250E2B 250 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton type MTE, industrial control transformer, pv: 240v x 480v, taps: none, sv: 24v, 55°C, 250 va
Product Type	250 Va Type Mte Control Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680422829
Manufacturers Part Number	C0250E2B
UPC	786680422829

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer

Packaging

Carton	1
Weight Per each	10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291

Uses, Certifications, and Standards

Application	Other
standard	UL Listed,cUL Certified,CSA Certified,RoHS Compliant
Temperature Rating	55°C