Thomas&Betts



Family

Catalog Number: Product ID: **UPC Number:** Status:

COND3/4SS 7TAD013020R0010 78620999312 Active

3/4 Inch Type 304 Stainless Steel Conduit with Type 304 Stainless Steel Coupling

- · Exceeds requirements for wash down applications
- Also available in marine grade-Type 316 stainless steel
- · Each 10 foot length of conduit ships with one Type 316 stainless steel conduit coupling
- · Type 316 stainless steel couplings are sold separately
- Type 304 stainless steel offers up to five times the lifespan when compared to standard galvanized steel conduit in corrosive environments
- · Water and wastewater treatment
- · Food and beverage processing
- Marine and coastal facilities
- · Pharmaceutical manufacturing
- · Pulp and paper processing
- Corrosive environments

· Meets stringent sanitary requirements

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Туре	Rigid/IMC Conduit Fittings
Special Features	Standard NPT Threads for Easy Installation
Application	Petrochemical Refining and Processing
Trade Size	3/4 Inch
Outside Diameter	1.05 Inch
Inside Diameter	0.824 Inch
Material	304 Stainless Steel
Color	Metallic
Packaging	
Outer Quantity	1000
Outer Dimensions (inches)	126x14.75x14
Weight Uom	1.09 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet

WSD-001049

For further technical assistance, please contact us...

ABB Installation Products Technical Support MS 3B-50

860 Ridge Lake Blvd. Memphis, TN 38120

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

ABB Installation Products - USA 860 Ridge Lake Blvd. Memphis, TN 38120 www.tnb.com