



BURNDY Catalog Number
UPC Number
Description
Status

C11HD4/0DB
 7818103477511
 GRD CL 1/2-1 DB 4/0HUB
 Active

Web Use
 BURNDY Product Line

Dimensional	
Pipe Size (Range)	1/2 -1
General	
Product Description	Cast Bronze Grnd Clamps, Water Pipe/Rebar/Grnd Rod -Grnd, Water Pipe- 1/2 " -1 " (13 -25) (Run), Rebar- #4 -#6 (Run)Grnd Rod -3/8 " -1 " (Run), Water Pipe- 1/2 " - 1 "(13 -25) (Run), Rebar #4-#6 (Run), Grnd Rod -3/8" - 1" (Run), Grnd-#8 - 4/0 (Tap)
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	8 AWG-4/0 AWG
Physical	
Type of Hardware	Steel - Zinc Plated
Product Material	Bronze Alloy
Approvals / Certifications	
UL Listed	Y
Rated for Direct Burial	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175