



## C250 250 Cu Long Barrel Compression Butt Splice

Nsi Industries

Catalog Number	C250
Manufacturer	Nsi Industries
Description	Long Barrel TINNEDCOPPERSPLICE250 MCM Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.2500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

### Dimensions and Weight

Size	L=3.25 - OD=.750 - ID=.590
------	----------------------------

### Descriptions

Description	250 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-250 250 MCM Copper Long Barre
Features	Long Barrel Tinned Copper Splice 250 MCM: Long Barrel Tinned Copper Splice is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Long Barrel TinnedCopperSplice250 MCM Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	250 MCM Copper Long Barrel Splice - Yellow
Special Features	250 MCM (STR) - CU Splice



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Manufacturer Information

Brand	NSi
GTIN	00662381037596
Manufacturers Part Number	C-250
UPC	662381037596

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice

## Packaging

Carton	1
Package	25
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C