

Eaton C25ANB125H

Catalog Number: C25ANB125H

Eaton definite purpose contactor, Quick, 25A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, Compact, single-pole, 25A, Contactor, Single-pole, 35A, Binding head screw and quick connect terminals (side-by-side), Non-reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C25ANB125H
UPC	Product Length/Depth
786685115832	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
0.47 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

defaultTaxonomyAttributeLabel

Amperage Rating

25A

Number Of Poles

Single-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

Compact, single-pole

Inductive full load

25 A

Model

Contactor

Resistive load

35 A

Terminals

Binding head screw and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25ANB 3D Model Xchange](#)

[C25ANB 2D PDF](#)

[C25ANB 3D Inventor](#)

[C25ANB AutoCAD 2D Footprint \(mm\)](#)

[C25ANB 2D Drawing Xchange](#)

[C25ANB AutoCAD 2D Footprint](#)

Specifications and datasheets

[Eaton Specification Sheet - C25ANB1.25H](#)

[Quick Selector - Definite Purpose Contactors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)