

# Eaton C25BNF240B

Catalog Number: C25BNF240B

Eaton definite purpose contactor, Quick, 40A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 40A, Contactor, Two-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25BNF240B
<b>UPC</b>	<b>Product Length/Depth</b>
786685116167	2.32 in
<b>Product Height</b>	<b>Product Width</b>
3.19 in	1.97 in
<b>Product Weight</b>	<b>Warranty</b>
0.6 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Recognized CSA Certified

## defaultTaxonomyAttributeLabel

### Amperage Rating

40A

### Number Of Poles

Two-pole

### Type

Non-reversing

### Coil

208-240 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

Compact, two-pole

### Inductive full load

40 A

### Model

Contactor

### Resistive load

50 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25BNF AutoCAD 2D Footprint \(mm\)](#)

[C25BNF 2D Drawing Xchange](#)

[C25BNF 2D PDF](#)

[C25BNF 3D Model Xchange](#)

[C25BNF AutoCAD 2D Footprint](#)

[C25BNF 3D Inventor](#)

### Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25BNF240B](#)