

# Eaton C25CNB130T

Catalog Number: C25CNB130T

Eaton definite purpose contactor, Quick, 30A, 277 Vac, 60 Hz, Open with metal mounting plate, Compact, single-pole w/shunt, 30A, Contactor, Single-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing

## General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25CNB130T
UPC	Product Length/Depth
786685116235	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
0.5 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

## defaultTaxonomyAttributeLabel

### Amperage Rating

30A

### Number Of Poles

Single-pole

### Type

Non-reversing

### Coil

24 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

Compact, single-pole with shunt

### Inductive full load

30 A

### Model

Contactors

### Resistive load

40 A

### Terminals

Binding head screw and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25CNB 3D Inventor](#)

[C25CNB 3D Model Xchange](#)

[C25CNB AutoCAD 2D Footprint](#)

[C25CNB 2D PDF](#)

[C25CNB 2D Drawing Xchange](#)

[C25CNB AutoCAD 2D Footprint \(mm\)](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25CNB130T](#)

[Quick Selector - Definite Purpose Contactors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)