



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNC330A 30A 3P 120V DP Opn Contactor

*Eaton Corp*

Catalog Number	C25DNC330A
Manufacturer	Eaton Corp
Description	
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

amperage rating	APPROXIMATE WEIGHT 21 LB; APPLICABLE STANDARD ANSI B1.20.1, ASME B16.11
coil	110-120 Vac, 50/60 Hz
dimensions	85.0900millimetreX60.9600millimetreX95.2500millimetre
Enclosure Type	Open with metal mounting plate
Frame Size	15-50A, two- and three-pole
inductive full load	APPROXIMATE WEIGHT 21 LB; APPLICABLE STANDARD ANSI B1.20.1, ASME B16.11
Poles	Three-pole
resistive load	40A
terminals	Screw/pressure plate

### Dimensions and Weight

Size	15-50A, two- and three-pole
------	-----------------------------

### Descriptions

Description	30A 3P 120V DP OPN CONTACTOR
Product Type	Definite Purpose Control - Contactor

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116307371
Manufacturers Part Number	C25DNC330A
Model	Contactor
UPC	782116307371

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
igcc	4755
Type	NON-REVERSING
unspsc code	39121529

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Motor and Power Control Equipment .....
Enclosure .....	Open with metal mounting plate .....
standard .....	UL Recognized; CSA Certified .....



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Definite Purpose Control - Contactor

**C25DNC330A**

**UPC:**782116307371

### Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

**Weight:**1.3 LB

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 30A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 40A
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNC330A](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data

