

Eaton C25DNC330A

Catalog Number: C25DNC330A

Eaton definite purpose contactor, Mounting plate, Quick, Pressure plate, 48 Vdc, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25DNC330A

UPC

782116307371

Product Length/Depth

3.35 in

Product Height

3.75 in

Product Width

2.4 in

Product Weight

1.19 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

CSA Certified

UL Recognized

UL Listed file E1491 (Guide Number NLDX2)



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Fuse block

Class G, 300 V, 60 A

Auxiliary contacts

Pressure plate

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Series

D1

Size

15 - 50A, two-pole and three-pole

Terminals

Screw

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DNC330A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)