

Eaton C25DND330C

Catalog Number: C25DND330C

Eaton definite purpose contactor, Quick, 30A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate and quick connect terminals (side-by-side), Non-reversing

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25DND330C
UPC	Product Length/Depth
782116308859	3.35 in
Product Height	Product Width
3.6 in	2.4 in
Product Weight	Warranty
1.1 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

440-480 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25DND3 3D Model Xchange](#)

[C25DND3 3D Inventor](#)

[C25DND3 AutoCAD 2D Footprint](#)

[C25DND3 AutoCAD 2D Footprint \(mm\)](#)

[C25DND3 2D Drawing Xchange](#)

[C25DND3 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DND330C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)