

Eaton C25DND330T

Catalog Number: C25DND330T

Eaton definite purpose contactor, Mounting plate, Quick, Pressure plate quick connect (side-by-side), 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, E1, Screw, Non-reversing



Photo is representative

General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DND330T
UPC	Product Length/Depth
782116300624	3.35 in
Product Height	Product Width
2.3 in	2.4 in
Product Weight	Warranty
1.15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
RoHS Compliant CE Marked	UL Listed file E1491 (Guide Number NLDX2) CSA Certified

defaultTaxonomyAttributeLabel

Accessories

Mounting plate

Number Of Poles

Three-pole

Type

Non-reversing

Auxiliary contacts

Pressure plate quick connect (side-by-side)

Coil voltage

24 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Model

Contactor

Series

E1

Terminals

Screw

Connection

Quick

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25DND3 AutoCAD 2D Footprint

C25DND3 2D PDF

C25DND3 AutoCAD 2D Footprint (mm)

C25DND3 3D Model Xchange

C25DND3 2D Drawing Xchange

C25DND3 3D Inventor

Specifications and datasheets

Eaton Specification Sheet - C25DND330T



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia