# Eaton C25DND330T

## Catalog Number: C25DND330T

Eaton definite purpose contactor, Mounting plate, Quick, Pressure plate quick connect (side-by-side), 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, E1, Screw, Non-reversing

# ILI 3L2 SL3 F.1 \*N FA Z5A @ C250DN0226 #017 C250DN0226 #017

### General specifications

Product Name Eaton definite purpose contactor

UPC 782116300624

Product Height 2.3 in

Product Weight 1.15 lb

Compliances

CE Marked

**RoHS** Compliant

C25DND330T Product Length/Depth 3.35 in

Catalog Number

Product Width 2.4 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E1491 (Guide Number NLDX2) CSA Certified



### defaultTaxonomyAttributeLabel

### Accessories

Mounting plate

### Number Of Poles

Three-pole

### Туре

Non-reversing

Auxiliary contacts Pressure plate quick connect (side-by-side)

Coil voltage

24 Vac, 50/60 Hz

Enclosure Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Model

Contactor

### Series

E1

### Terminals

Screw

### Connection

Quick

### Resources

# Catalogs Eaton's Volume 5—Motor Control and Protection Drawings C25DND3 3D Model Xchange C25DND3 2D PDF C25DND3 2D Drawing Xchange C25DND3 3D Inventor C25DND3 AutoCAD 2D Footprint C25DND3 AutoCAD 2D Footprint (mm) Specifications and datasheets Eaton Specification Sheet - C25DND330T



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights Reserved. All other trademarks are owners.



Eaton.com/socialmedia