



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DNF325T Open N-R 3P 25A DP Cont Box Lugs W/QC Term 24VAC C *Eaton Corp*

Catalog Number	C25DNF325T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Mounting Plate, Quick, Quick Connect , 12 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and 3P, 25A, Contactor, 3P, Global Listed, D1, Box Lugs (Posidrive Setscrew), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Coil Voltage	120 Vdc
connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 3.7500 IN
Enclosure Type	Open with metal mounting plate

Descriptions

Description	OPEN N-R 3P 25A DP CONT BOX LUGS W/QC TERM 24VAC C
extra long description	ETN C25DNF325T OP N-R 3P 25ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing
Product Type	Op N-R 3P 25ADPCNT BXLGS W/Qc24ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300570
Manufacturers Part Number	C25DNF325T
UPC	782116300570

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Weight Per each	1.19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

standard

UL Recognized, CSA Certified, UL Listed file E1491 (Guide Number
NLDX2), RoHS Compliant