

# Eaton C25DNF325T

Catalog Number: C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF325T
UPC	Product Length/Depth
782116300570	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
1.19 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized
	CSA Certified
	UL Listed file E1491 (Guide Number NLDX2)

## defaultTaxonomyAttributeLabel

### Amperage Rating

25A

### Number Of Poles

Three-pole

### Options

Global listed

### Type

Non-reversing

### Auxiliary contacts

Quick connect (side-by-side)

### Coil

24 Vac, 50/60 Hz

### Coil voltage

120 Vdc

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

30 A

### Model

Contactor

### Resistive load

35 A

### Series

D1

### Terminals

Box lugs (posidrive setscrew)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DNF325T](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)