

# Specifications



Photo is representative



## Eaton C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

<b>PRODUCT NAME</b>	Eaton definite purpose contactor
<b>CATALOG NUMBER</b>	C25DNF330T
<b>UPC</b>	782116311422
<b>PRODUCT LENGTH/DEPTH</b>	3.35 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	2.4 in
<b>PRODUCT WEIGHT</b>	1.19 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Recognized UL Listed
<b>PRODUCT TYPE</b>	Definite purpose contactor



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	30A
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Non-reversing
<b>AUXILIARY CONTACTS</b>	Pressure plate and quick connect
<b>COIL</b>	24 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	1 NO, 1 NC
<b>ENCLOSURE</b>	Open with metal mounting plate
<b>FRAME SIZE</b>	15-50 A, two-pole and three-pole
<b>INDUCTIVE FULL LOAD</b>	30 A
<b>MODEL</b>	Contactora
<b>RESISTIVE LOAD</b>	40 A
<b>TERMINALS</b>	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
<b>CONNECTION</b>	Quick

## Resources

CATALOGS	<a href="#">Motor Control and Protection, Definite Purpose Contactors and Starters, Volume 5, Tab 4</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C25DNF330T</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

<b>PRODUCT NAME</b>	Eaton definite purpose contactor
<b>CATALOG NUMBER</b>	C25DNF330T
<b>UPC</b>	782116311422
<b>PRODUCT LENGTH/DEPTH</b>	3.35 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	2.4 in
<b>PRODUCT WEIGHT</b>	1.19 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Recognized UL Listed
<b>PRODUCT TYPE</b>	Definite purpose contactor



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	30A
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Non-reversing
<b>AUXILIARY CONTACTS</b>	Pressure plate and quick connect
<b>COIL</b>	24 Vac, 50/60 Hz
<b>CONTACT CONFIGURATION</b>	1 NO, 1 NC
<b>ENCLOSURE</b>	Open with metal mounting plate
<b>FRAME SIZE</b>	15-50 A, two-pole and three-pole
<b>INDUCTIVE FULL LOAD</b>	30 A
<b>MODEL</b>	Contactora
<b>RESISTIVE LOAD</b>	40 A
<b>TERMINALS</b>	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
<b>CONNECTION</b>	Quick

## Resources

CATALOGS	<a href="#">Motor Control and Protection, Definite Purpose Contactors and Starters, Volume 5, Tab 4</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C25DNF330T</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

