



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNF330T 3P 30A 24V DP Contactor

Eaton Corp

Catalog Number	C25DNF330T
Manufacturer	Eaton Corp
Description	Definite Purpose Control - Contactor, 3 Poles, 30 A, 24 V Ac, 40 A Resistive Load, 15 to 50 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.35 In Overall Length, 2.40 In Overall Width, 1.19 LB
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

amperage rating	APPROXIMATE WEIGHT 21 LB; APPLICABLE STANDARD ANSI B1.20.1, ASME B16.11
coil	24 Vac, 50/60 Hz
connection	Quick
dimensions	85.0900millimetreX60.9600millimetreX76.2000millimetre
inductive full load	APPROXIMATE WEIGHT 21 LB; APPLICABLE STANDARD ANSI B1.20.1, ASME B16.11
Poles	Three-pole
terminals	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Descriptions

Description	3P 30A 24V DP CONTACTOR
-------------	-------------------------

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116311422
Model	Contactor
UPC	782116311422

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
igcc	4755
Type	NON-REVERSING
unspsc code	39121529

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Enclosure ..... Open with metal mounting plate .....  
standard ..... UL Recognized; CSA Certified .....



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Definite Purpose Control - Contactor

**C25DNF330T**

**UPC:**782116311422

### Dimensions:

- **Height:** 3 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

**Weight:**.9 LB

### Warranties:

- 1 year

### Specifications:

- **Connection:** Quick
- **Amperage Rating:** 30A
- **Coil:** 24 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 40A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNF330T](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data

