

# Eaton C25DNF340B

Catalog Number: C25DNF340B

Eaton definite purpose contactor, Quick, Open with metal mounting plate, 15-50A, two-and three-pole, Contactor, Quick connect ,208-240 Vac, 50/60 Hz



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25DNF340B
<b>UPC</b>	<b>Product Length/Depth</b>
782116300686	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.4 in
<b>Product Weight</b>	<b>Warranty</b>
1.05 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Recognized CSA Certified

**Amperage Rating**

40A

**Number Of Poles**

Three-pole

**Type**

Non-reversing

**Coil**

208-240 Vac, 50/60 Hz

**Contact configuration**

1 NC

**Enclosure**

Open with metal mounting plate

**Frame size**

15-50 A, two-pole and three-pole

**Inductive full load**

40 A

**Model**

Contactor

**Resistive load**

50 A

**Terminals**

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

**Connection**

Quick

**Catalogs**[Eaton's Volume 5—Motor Control and Protection](#)**Drawings**[C25DNF3 AutoCAD 2D Footprint](#)[C25DNF3 2D Drawing Xchange](#)[C25DNF3 3D Model Xchange](#)[C25DNF3 3D Inventor](#)[C25DNF3 2D PDF](#)[C25DNF3 AutoCAD 2D Footprint \(mm\)](#)**Specifications and datasheets**[Eaton Specification Sheet - C25DNF340B](#)