



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST  
72712-0000, AR Bentonville  
Phone: 479-250-1930  
Fax: 479-250-1931



## C25DNF340C Open N-R 3P 40A DP Cont Box Lugs W/QC Term 480vac *Eaton Corp*

Catalog Number	C25DNF340C
Manufacturer	Eaton Corp
Description	Definite Purpose Control - Contactor, 3 Poles, 40 A, 440 to 480 V Ac, 40 A Resistive Load, 1/3 Phases, 7-1/2 HP (Single Phase);10 HP (Three Phase);5.5 KW (Single Phase);7.5 KW (Three Phase) Motor Power, 15 to 50 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.35 In Overall Length, 2.40 In Overall Width, 1.19 LB
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Enclosure Type	Open with metal mounting plate
induct amp/res amp rating	40/50
Voltage Rating	480

### Dimensions and Weight

Depth	3.35
Height	2.75
Width	2.4

### Descriptions

Description	OPEN N-R 3P 40A DP CONT BOX LUGS W/QC TERM 480VAC
extra long description	ETN C25DNF340C OP N-R 3P 40ADPCNT B

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116311651
UPC	782116311651

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.19

### Uses, Certifications, and Standards

standard	CSA Certified,UL Recognized,UL Listed file E1491 (Guide Number NLDX2),RoHS Compliant
----------	--