

# Eaton C25DNF350T

Catalog Number: C25DNF350T

Eaton definite purpose contactor, Quick, 50A, 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, Contactor, Three-pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C25DNF350T
<b>UPC</b>	<b>Product Length/Depth</b>
782116311996	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	2.4 in
<b>Product Weight</b>	<b>Warranty</b>
1.33 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	CSA Certified
	UL Recognized

## defaultTaxonomyAttributeLabel

### Amperage Rating

50A

### Number Of Poles

Three-pole

### Type

Non-reversing

### Coil

24 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

50 A

### Model

Contactora

### Resistive load

65 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DNF350T](#)