

# Eaton C25ENF440A

Catalog Number: C25ENF440A

Eaton definite purpose contactor, Quick, 50A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 50A, Contactor, Three-pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing

## General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25ENF440A
UPC	Product Length/Depth
782113475578	3.38 in
Product Height	Product Width
3.75 in	2.68 in
Product Weight	Warranty
2.15 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

## Catalog Notes

Resistive Load rating per pole

## defaultTaxonomyAttributeLabel

### Amperage Rating

40A

### Number Of Poles

Four-pole

### Type

Non-reversing

### Coil

24 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

40 A

### Model

Contactor

### Resistive load

50 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25ENF4 3D Inventor](#)

[C25ENF4 AutoCAD 2D Footprint](#)

[C25ENF4 3D Model Xchange](#)

[C25ENF4 AutoCAD 2D Footprint \(mm\)](#)

[C25ENF4 2D Drawing Xchange](#)

[C25ENF4 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25ENF440A](#)