

# Eaton C25FNF360B

Catalog Number: C25FNF360B

Eaton definite purpose contactor, Quick, 60A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 60A, Contactor, Three-pole, 75A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

## General specifications



Photo is representative

Product Name

Eaton definite purpose contactor

UPC

782113476148

Product Height

3.75 in

Product Weight

2.65 lb

Compliances

RoHS Compliant

Catalog Number

C25FNF360B

Product Length/Depth

3.97 in

Product Width

2.63 in

Warranty

1 year

Certifications

CSA Certified

UL Recognized

Catalog Notes

Resistive Load rating per pole

defaultTaxonomyAttributeLabel

Amperage Rating

60A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

208-240 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

60 A

Model

Contactor

Resistive load

75 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25FNF3 2D PDF

C25FNF3 3D Inventor

C25FNF3 AutoCAD 2D Footprint (mm)

C25FNF3 AutoCAD 2D Footprint

C25FNF3 3D Model Xchange

Specifications and datasheets

Eaton Specification Sheet - C25FNF3 60B



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia