



C30 3/0 Cu Long Barrel Compression Butt Splice

Nsi Industries

Catalog Number	C30
Manufacturer	Nsi Industries
Description	Long Barrel Tinnedcoppersplice 3/0 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.1500 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Orange
Finish	Tin Plated

Dimensions and Weight

Size	L=2.25 - OD=.620 - ID=.490
------	----------------------------

Descriptions

Description	3/0 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-3/0 3/0 AWG Copper Long Barre
Features	Long Barrel Tinned Copper Splice 3/0 AWG: Long Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Long Barrel TinnedCopperSplice 3/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	3/0 Awg Copper Long Barrel Splice - Orange
Special Features	3/0 AWG (STR) - CU Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 Cavitt Avenue
77801-0000, TX Bryan
Phone: 979-779-6630
Fax: 979-779-6620

Manufacturer Information

Brand	NSi
GTIN	00662381037572
Manufacturers Part Number	C-3/0
UPC	662381037572

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice

Packaging

Carton	1
Package	25
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C